





PART NO.	"D" ^{+0.0} _{-0.1}	"d" ^{+0.2} _{-0.1}	MATERIAL	"L"
*OFBLT-2.6-05-PP	5.05	2.6	POLYPROPYLENE, WHITE (RMS-86)	100 METERS
OFBLT-3.1-05-PP		3.1		
OFBLT-4.2-635-PP	6.35	4.2		
OFBLT-3.1-05-PBT VO	5.05	3.1	PBT VO, BLACK UL94-VO RATED (RMS-140)	
OFBLT-4.2-635-PBT VO	6.35	4.2		

*PARTS AVAILABLE BY SPECIAL ORDER ONLY



NOTES:
1. PLENUM RATED TYPE
AVAILABLE BY SPECIAL ORDER ONLY.

APPLICABLE PATENTS: CANADA PAT. NO.2122064
AUSTRALIA PAT. NO. 29063/92
EUROPE PAT. NO. 92923018.3
USA PAT. NO. 5 473 723

TITLE: OPTICAL FIBER BEND LIMITING TUBE			DWG IN mm		FINAL		 	
F	SEE CO 200318 FOR CHANGES	SK 02.03.09	TOLERANCES UNLESS NOTED	FILE # OFBLT	DWN: AM	APP:	PART #	
E	SEE CO 200035 FOR CHANGES	SK 09.26.07	.XX=	MAT'L: SEE TABLE	DT: 5/14/99	DT:	SEE TABLE	
D	SEE ECN #1012 FOR CHANGES	SK 06.03.05	.XXX=	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		PRINT TYPE	
C	ADDED RMS NOTE TO TABLE	SJ 04.24.02	FRAC=					CA
B	REMOVED P/N: OFBLT-2.6-05-PBT VO	SM 02.05.02	ANG=±1°					
A	UPDATED PRINT, CHANGED FILE NO.	SM 01.31.02						
REV	DESCRIPTION	ENGR DATE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[OFBLT-31-05V0](#) [OFBLT-42-635PP](#) [OFBLT-3.1-05-PP](#)