

## MOSA M12 MALE 0° FIELD-WIREABLE (IDC)

D-cod., 4-pol., 0,25-0,34mm<sup>2</sup>, shielded

Male M12, straight  
Field-wireable (IDC terminals)  
D-coded, 4-pole, shielded, CAT 5

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.25...0.34 mm <sup>2</sup> (AWG 22...24)
Sealing range (cable diameter)	5.5...8.8 mm
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

#### General data

Temperature range	-40...+85 °C
-------------------	--------------

#### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1