

CARDMASTER PC 25/22-C3



Order symbol: PC 25/22-C3
Product nbr: 7520141
Description: Enclosure, PC
Remarks: Without main cover

EAN: 6418074059352
El. number:
 Finland: 3422959
 :

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		257	219	122	Ingress Protection (EN 60529): IP 65
inch:		10.1	8.6	4.8	Impact Resistance (EN 62262): IK 08/07
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Gasket material:		EPDM			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MP 25/22		Mounting plate			
FP 25/22		Front plate (aluminium)			
FC PC 25/22		Frame of PC front plate			
Certificates:					
		Underwriters Laboratories			
		Fimko			
		Europe EN 62208: 2003			
		UL Canada			
		Gost R			

