
PRODUCT-DETAILS

KSU00810

SST 304 - 8MM INNER DIAMETER



General Information

Extended Product Type	KSU00810
Product ID	7TCA297070R0065
EAN	5011949017368
Catalog Description	SST 304 - 8MM INNER DIAMETER
Long Description	Very Flexible, Small Bore Conduit, Nominal Conduit Size 8mm, Outside Diameter 10.1mm, Inside Diameter 8.0mm, Static Bend Radius 17.5mm, Reel Length 10 Meters, IP40 Rating, Uncovered 304 Stainless Steel, Metallic

Additional Information

Application	Indoors - Light Industrial, Buildings Marine, Corrosive Environments
Product Type	Flexible, Metallic Conduit

Ordering

EAN	5011949017368
UPC	786210308531
Customs Tariff Number	8307106000

Dimensions

Product Net Depth / Length	10 m
----------------------------	------

Technical

Number of Batteries	0
Color	Metallic
Material	304 Stainless Steel

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	1 in 25 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	KSU00810
Instructions and Manuals	KSU00810
Declaration of Conformity - CE	9AKK107492A9617
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

Classifications

ETIM 8	EC001179 - Protective metallic hose
UNSPSC	39131706

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

