

8 7 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



6

5

5



NOTES

D

С

T-Rev.D


8

MATERIAL BRACKET: NICKEL SILVER ALLOY. KEYSTONE JACK HOUSING: ZINE ALLOY, NICKEL PLATED. C8 REAR HOUSING: ZINC ALLOY, NICKEL PLATED. KEYSTONE JACK LATCH: PC+ABS, UL94V-0. .76 .63 - House Hunder CONTACT HOLDER: PC, UL94V-0. [19.20]16.00] JACK CONTACTS: PHOSPHOR BRONZE, 50U" GOLD PAINTING. IDC PLASTIC: PC, UL94V-0. IDC TERMINALS: PHOSPHOR BRONZE, TIN OVER NICKEL UNDERCOAT. PHYSICAL CHARACTERISTICS INSERTION LIFE: 750 MATING CYCLES WITH FCC COMPLIANT 8P PLUG. CONTACT FORCE: 100 GRAMS WITH FCC COMPLIANT 8P PLUG. PLUG RETENTION FORCE: 11 LBF MIN. В DURABILITY: 30 TERMINATION CYCLES. CONTACT COMPATIBILITY: ACCOMMODATES 22 TO 24 AWG SOLID. OPERATING TEMPERATURE RANGE: -10° C TO + 60° C. STORAGE TEMPERATURE RANGE: -40° C TO + 68° C. HUMIDITY: 10% ~ 90% RH (NON-CONDENSING). ELECTRICAL INSULATION RESISTANCE: 500 MQ MINIMUM. DC CURRENT RATING: 1.5 Amps. INPUT TO OUTPUT D.C. RESISTANCE: 100 mQ MAXIMUM CONTACT RESISTANCE: 20 mQ MAXIMUM. VOLTAGE PROOF (CONTACT TO CONTACT): 1000 V AC. VOLTAGE PROOF (CONTACT TO SHIELD): 1500 V DC. **MISCELLANEOUS** А KIT TO BE SHIPPED WITH 1X IDC CAP, 1X NYLON CABLE TIE, 1XINSTRUCTION ONLY ACCEPT RJ-45 8P8C PLUG. ACCORDING TO: ANSI/TIA-568.2-D, ISO/IEC 11801-1, IEC 60603-7, IEEE 802.3BT POWER OVER ETHERNET PLUS PLUS (POE++) APPLICATION,

IEEE 602.361 FOWER OVER EITERNET FLOS FLOS (FOE++) AFFLICATION, IEC 60512-99-002 MATING AND UN-MATING CONNECTORS UNDER ELECTRICAL LOAD KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

6

7




3

REV

2 REVISIONS

DESCRIPTION




DATE

APPROVED

GUTTADAURO

ID

С



SUGGESTED MOUNTING CUTOUT

	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE			North Andover,	Street, West Mill, ndover, MA 01845 US.				
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0	DRAWN BY DCUI	02/19/2020	an INFINIT [®] brand Phone: 1.800.341.5266 1.978.682.6936							
	>12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0	CHECKED BY BZHANG	02/19/2020	CATEGORY							A
	>120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	APPROVED BY GUTTADAURO	02/19/2020	TELECOM/MODU				MODULAR			
ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$ (5) $XX = \pm .02$ (.5) $XX = \pm .005$ (.13) THIRD-ANGLE PROJECTION THIRD-ANGLE PROJECTION		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CATEGORY 8 SHIELDED KEYSTONE JACK RJ45/TL POE++							
		COLOR VARIATIONS MAY OCCUR		size A	CAGE CODE 43321		dwg. no. R	RJTLC8S-PO	E	REV.	
				SCALE: NONE		CAD FILE: RJTLC8S-POE		E.SLDDRW	SHEET 1 (OF 1	
	↑ /	ا ع		1 2		2		Ι,	1		