

## preLink RJ45 HIFF module empty



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 000 0002
Specification	preLink RJ45 HIFF module empty
HARTING eCatalogue	<a href="https://b2b.harting.com/20820000002">https://b2b.harting.com/20820000002</a>

### Identification

Category	Connectors
Series	preLink®
Element	Female module
Specification	without terminal block

### Version

Termination method	preLink® IDC insulation displacement termination
Size	HIFF version

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP20
Transmission characteristics	Cat. 6A Class EA up to 500 MHz
Vibration resistance	5.72 m/s <sup>2</sup> acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances No

## Specifications and approvals

Approvals DNV GL

UL / CSA UL 1863 DUXR2.E470046  
CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046

PROFINET Yes

## Commercial data

Packaging size 1

Net weight 22 g

Country of origin Latvia

European customs tariff number 85366990

eCl@ss 27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[20820000002](#)