



PCB Layout

NOTES :

- △ MATERIALS AND FINISH:
 - HOUSING: PA66
 - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
- 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (RoHS)
- 3. WIRE TYPES AND SIZES ACCEPTED
- WIRE RANGE: 14AWG~28AWG.
- STRIP LENGTH: 10mm
- 4. PACKAGED IN TRAY.
- 5. CURRENT RATING: 16amp AC300V.
- 6. OPERATION TEMPERATURE: -40°C TO +105°C
- 7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834076
- THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834076

REV. NO.	DATE	BY	APP'D
1			

REV. NO.	DESCRIPTION	DATE	BY	APP'D
1				

NO. OF POSITIONS	PART NO.
① HOUSING	2834076-1
② CONTACT	2834076-2
③ LEVER	2834076-3
④ COVER	2834076-4
⑤ SPRING	2834076-5
⑥ HOUSING	2834076-6
⑦ POSN	2834076-7
⑧ POSN	2834076-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

REVISIONS

REV. NO.	DATE	BY	APP'D
1			

REV. NO.	DESCRIPTION	DATE	BY	APP'D
1				

UNLESS OTHERWISE SPECIFIED

UNIT	MM
TOLERANCE	±0.1
ANGLE	±0.5
THREAD	AS PER STANDARD

TE Connectivity

5.00mm 45° Entry Screwless Connector

SIZE: A200779 C-2834076

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2834076-1](#)