

3M™ 314D Cloth Belt



Product Construction

<i>Mineral</i>	Aluminum oxide
<i>Bonding</i>	Resin bond.
<i>Backing</i>	J-cloth.
<i>Coating</i>	Open coat.
<i>Grit Range</i>	P40 – P400
<i>Size</i>	

Type	Size
Roll	50 mm x 25 mt
Roll	115 mm x 50 mt
Sheet	230 mm x 280 mm

Available Forms



f

Applications

Materials:
Wood, metal and plastic

Recommendation

f Recommended for manual applications

f

f

f

f

3M™ 314D Cloth Belt

Features

Flexible cloth-backing

Advantages

Off hand grinding on edges, corners and rounded areas

Benefits

Saves time and money



Semi-open coat

Reduces surface loading; good cutting performance

Extended product life especially on scaled/dirty surfaces



Resin bond

Good mineral anchorage; reduced shelling

Longer product life



Machines



Safety



Quality

3M Plants are ISO 9002 certified.

Product Use: All statements, technical information and recommendations contained in this document are based on tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.



3M Italia SpA
Reperto ASD Abrasivi Industriali
Via Norberto Bobbio,21
20069 – Pioltello Milano
Tel: 02 7035 2529
Fax: 02 93660172

Data Sheet: 314D
Issued 06/11
© 3M 2011. All rights reserved.