



## Main

Commercial Status	Commercialised
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Pre-wired connectors
Series name	General purpose
Electrical connection	Straight female connector M12, 5 pins (included earth pin)
Collar material	Metal
Status LED	Without
Cable length	5 m

## Complementary

Cable connector fixing	Screw-on
Cable outer diameter	5.9 mm
Cable composition	5 x 0.34 mm <sup>2</sup>
Wire insulation material	PUR
[Ue] rated operational voltage	36 V DC 30 V AC
[In] rated current	4 A
Contact resistance	<= 5000 µOhm
Insulating resistance	>= 1 GΩ
Product weight	0.27 kg

## Environment

IP degree of protection	IP67
Ambient air temperature for operation	-5...80 °C (flexing) -40...80 °C (static)
Ambient air temperature for storage	-40...80 °C

## Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0649 - <a href="#">Schneider Electric declaration of conformity</a>