



SKU	LENGTH (m)
A50FBLCLC1	1.0
A50FBLCLC2	2.0
A50FBLCLC3	3.0
A50FBLCLC5	5.0
A50FBLCLC7	7.0
A50FBLCLC10	10.0
A50FBLCLC15	15.0

No	Part	Material / color
1	Dust cap	TPV / white
2	LC housing	PEI / beige
3	LC duplex clip	PEI / beige
4	LC boot 1	TPV / red
5	LC boot 2	TPV / black
6	Ferrule	Ceramic
A	OM3 fiber	Glass
B	Buffer 1	LSZH / white
C	Buffer 2	LSZH / orange
D	Yarn	Kevlar / yellow
E	Jacket	LSZH / aqua
	Tube	Teflon
	Spring	SUS

THIRD ANGLE PROJECTION

# StarTech.com

<b>GENERAL NOTES</b>		PRODUCT ID		A50FBLCLCxx
DIMENSIONS ARE IN MM - DO NOT SCALE		DESCRIPTION		LC/UPC to LC/UPC OM3 Multimode Fiber Optic Cable
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM		<b>DO NOT SCALE</b>	SHEET: 1 OF: 1	UPLOAD DATE: 1/10/2023