

## Patch cable - FL CAT5 PATCH 0,3 - 2832250

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Patch cable, CAT5, assembled, 0.3 m



Ethernet

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 043984
GTIN	4046356043984

### Technical data

#### Cable type

Smallest bending radius, fixed installation	50 mm (under load)
Cable structure	2x2xAWG26/7; SF/UTP
Smallest bending radius, movable installation	25 mm (without load)
Shielding	SF/UTP

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

#### External sheath

Outer sheath, material	LSFROH
External diameter	5.80 mm
External diameter max.	6 mm

#### Single wire

Single wires, quantity	8
Single wire, material	Cu litz wire
Single wire, cross section	0.14 mm <sup>2</sup>

#### Plug

Connection profile	RJ45
--------------------	------

# Patch cable - FL CAT5 PATCH 0,3 - 2832250

## Technical data

### Mechanical properties

Smallest bending radius, fixed installation	30 mm
---	-------

### General

Nominal voltage $U_N$	150 V <sub>rms</sub>
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps
Contact resistance	≤ 0.003 Ω (IEC 60603-7)

### Behavior in fire

Flame resistance	according to IEC 60332-3C
Concentration of fumes	in accordance with IEC 61034
Halogen-free	according to IEC 60754-1

### Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Flame resistance	according to IEC 60332-3C
Halogen-free	according to IEC 60754-1
Flammability rating according to UL 94	V0

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27060308
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	27259200
eCl@ss 5.1	27259200
eCl@ss 6.0	27259200
eCl@ss 7.0	27060308
eCl@ss 8.0	27060308
eCl@ss 9.0	27060308

### ETIM

ETIM 2.0	EC001262
ETIM 3.0	EC001262
ETIM 4.0	EC001262
ETIM 5.0	EC002599
ETIM 6.0	EC001262
ETIM 7.0	EC001262

# Patch cable - FL CAT5 PATCH 0,3 - 2832250

## Classifications

### UNSPSC

UNSPSC 6.01	26121609
UNSPSC 7.0901	26121609
UNSPSC 11	26121609
UNSPSC 12.01	26121609
UNSPSC 13.2	26121604
UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

## Approvals

### Approvals

#### Approvals

DNV GL / EAC / DNV GL / EAC

#### Ex Approvals

### Approval details

DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAE000020G
--------	---	---	------------

EAC			19060508
-----	---	--	----------

DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAE000020G
--------	---	---	------------

EAC			19060508
-----	---	--	----------

## Accessories

### Accessories

## Patch cable - FL CAT5 PATCH 0,3 - 2832250

### Accessories

#### Color-coding

Color-coding - FL PATCH CCODE BK - 2891194



Color marking for patch cable, black

---

Color-coding - FL PATCH CCODE BN - 2891495



Color marking for patch cable, brown

---

Color-coding - FL PATCH CCODE BU - 2891291



Color marking for patch cable, blue

---

Color-coding - FL PATCH CCODE GN - 2891796



Color marking for patch cable, green

---

Color-coding - FL PATCH CCODE GY - 2891699



Color marking for patch cable, gray

---

## Patch cable - FL CAT5 PATCH 0,3 - 2832250

### Accessories

Color-coding - FL PATCH CCODE RD - 2891893



Color marking for patch cable, red

---

Color-coding - FL PATCH CCODE VT - 2891990



Color marking for patch cable, purple

---

Color-coding - FL PATCH CCODE YE - 2891592



Color marking for patch cable, yellow

---

### Safety locking

Port Guard Security Element - FL PATCH GUARD - 2891424



Lockable security element

---

Port Guard Security Element - FL PATCH SAFE CLIP - 2891246



Security element for FL patch cable

---

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2832250](#)