


0220 - HEXAGON HEADED BSP PARALLEL AND METRIC THREAD



maximum working pressure 20 bar
 2 MPa
 290 psi
working temperature -20 to 80 °C
 -4 to 176 °F
 253 to 353 °K
body BRASS
sealing washer TECHNICAL POLYMER

Part Nb	C	F (mm)	ØG (mm)	H1 (mm)	 (kg)
	All ▾	All ▾	All ▾	All ▾	All ▾
0220 10 00	G1/8	14	14	7.5	.011
0220 13 00	G1/4	17	17	7.5	.02
0220 17 00	G3/8	17	22	8.5	.024
0220 19 00	M5x0,8	8	8	5	.002
0220 21 00	G1/2	22	27	10	.041