




## 0448 - 3 WAY BALL VALVE PANEL MOUNTABLE FEM. RIGHT ANGLED



<b>maximum working pressure</b>	20 bar 2 MPa 290 psi
<b>working temperature</b>	-20 to 80 °C -4 to 176 °F 253 to 353 °K
<b>adjustment screw</b>	NICKEL PLATED BRASS
<b>body</b>	NICKEL PLATED BRASS
<b>retaining nut</b>	NICKEL PLATED BRASS
<b>stem</b>	BRASS
<b>stem seal</b>	NBR
<b>'O'-rings</b>	NBR
<b>ball seal</b>	NBR
<b>handle</b>	ZAMAK




Part Nb	C	E (mm)	F (mm)	F1 (mm)	H (mm)	H1 (mm)	H2 (mm)	H3 (mm)	J (mm)	L (mm)	L1 (mm)	M (mm)	ØT (mm)	 (kg)
	All	All	All	All	All	All	All	All	All	All	All	All	All	All
0448 04 10	G1/8	8	14	22	37	14	18	12	14	44	25	48	16.5	.126
0448 06 13	G1/4	12	19	24	45	19	24	14	22	53	28	48	20.5	.23
0448 09 17	G3/8	12	24	27	50	21	27	21	25	59	31	69	20.5	.328
0448 12 21	G1/2	15	27	27	51	23	33	21	29	67	34	69	20.5	.392