



3102 - EQUAL AND UNEQUAL ELBOW



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
vacuum capability	755 mm Hg
body	TECHNICAL POLYMER
'O'-rings	NBR
gripping ring	STAINLESS STEEL

Part Nb	ØD (MM)	ØD1 (MM)	ØG (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾
3102 04 00	4	4	8.5	19	.001
3102 04 06	4	6	10.5	22.5	.003
3102 06 00	6	6	10.5	22.5	.002
3102 06 08	6	8	13.5	29.5	.008
3102 08 00	8	8	13.5	29.5	.004
3102 08 10	8	10	16	34.5	.011
3102 10 00	10	10	16	34.5	.006
3102 10 12	10	12	19	40.5	.019
3102 12 00	12	12	19	40.5	.01
3102 14 00	14	14	22	46.5	.015
3102 16 00	16	16	27	52	.043