

Datasheet

RS Line Mounting Hydraulic Flow Control Valve, G 1/8

RS Stock number 390-7724



Body Material	Steel
Connection Port Thread	G 1/8
Maximum Flow Rate	6.2L/min
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Seal Material	Nitrile Rubber
Thread Size	1/8 in
Thread Standard	G