

Datasheet

RS Line Mounting Hydraulic Flow Control Valve, G 1/4

RS Stock number 390-7730



Body Material	Steel
Connection Port Thread	G 1/4
Maximum Flow Rate	13.5L/min
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Seal Material	Nitrile Rubber
Thread Size	1/4 in
Thread Standard	G