

- Warm White
- Neutral White
- Cold White
- Amber
- Red
- Green
- Blue



FEATURES

- Mercury free, no UV or IR emissions.
- DC12V/24V
- 12watts/m
- 5000Hrs LED life time
- Dimmable
- CE,Rohs,UL,cUL

SPECIFICATIONS

Length	5 meters/Roll
Power	12watts/m
Width	8/10mm
LED Qty	60LED/m
Input Voltage	12/24VDC
Lumen	20-22lm/LED
PCB	2, 3 OZ
CRI	70+, 80+,90+,95+
Waterproof	IP54/IP65/IP67/IP68
Lm/m	1000

STRUCTURE









Long life span
50,000
hours

12
VDC

Cut into
3 segments

5m

120°

3
YEARS
WARRANTY