

# LED Signalleuchten LED Panel Mount Indicators

EINBAUDURCHMESSER  
MOUNTING HOLE

6 mm

8 mm

12 mm

14 mm

16 mm

19 mm

22 mm


ZUBEHÖR  
ACCESSORIES

## Außenreflektor dreifarbig ohne Vorwiderstand IP40 / Prominent (exterior) bezel tri-colour without resistor IP40



Part Number	Colour	Typ. Forward Voltage	Typ. Current	Typ. Lumi. Intensity
<b>Hochglanzverchromter Metallreflektor / Satin chrome bezel</b>				
19120004	red/green/yellow	2,1/2,2/2,2V DC	–	10/20/30mcd at 20mA
<b>Schwarzverchromter Metallreflektor / Black chrome bezel</b>				
19121004	red/green/yellow	2,1/2,2/2,2V DC	–	10/20/30mcd at 20mA
<b>Mattverchromter Metallreflektor / Matt chrome bezel</b>				
19122004	red/green/yellow	2,1/2,2/2,2V DC	–	10/20/30mcd at 20mA

Maximale Frontplattenstärke 5,5mm / Maximum panel thickness 5.5mm



## Außenreflektor dreifarbig mit Vorwiderstand IP67 / Prominent (exterior) bezel tri-colour with resistor IP67



Part Number	Colour	Voltage	Typ. Current	Typ. Lumi. Intensity
<b>Hochglanzverchromter Metallreflektor / Satin chrome bezel</b>				
19TR0A12	red/green/yellow	12V DC	20/20/40mA DC	10/20/30mcd
19TR0A24	red/green/yellow	24V DC	15/15/30mA DC	8/15/23mcd
<b>Schwarzverchromter Metallreflektor / Black chrome bezel</b>				
19TR1A12	red/green/yellow	12V DC	20/20/40mA DC	10/20/30mcd
19TR1A24	red/green/yellow	24V DC	15/15/30mA DC	8/15/23mcd
<b>Mattverchromter Metallreflektor / Matt chrome bezel</b>				
19TR2A12	red/green/yellow	12V DC	20/20/40mA DC	10/20/30mcd
19TR2A24	red/green/yellow	24V DC	15/15/30mA DC	8/15/23mcd

Maximale Frontplattenstärke 5,5mm / Maximum panel thickness 5.5mm  
Andere Spannungen auf Anfrage / Other voltages on request

