



3108 - MALE STUD RUN TEE, BSPT AND NPT THREAD



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-20 to 80 °C -4 to 176 °F 253 to 353 °K
vacuum capability	755 mm Hg
body	TECHNICAL POLYMER
sub-base	NICKEL PLATED BRASS
'O'-rings	NBR
gripping ring	STAINLESS STEEL
surface treatment	PTFE

Part Nb	ØD (MM)	C	F (mm)	ØG (mm)	H (mm)	L2 (mm)	L_2 (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾		All ▾	All ▾
3108 04 10	4	R1/8	10	8.5	15.5		14	.006
3108 04 13	4	R1/4	14	8.5	16		14	.015
3108 06 10	6	R1/8	10	10.5	17.5		16	.007
3108 06 13	6	R1/4	14	10.5	18		16	.016
3108 08 10	8	R1/8	10	13.5	22		23	.009
3108 08 13	8	R1/4	14	13.5	21		23	.016
3108 08 17	8	R3/8	17	13.5	21		23	.02
3108 10 13	10	R1/4	15	16	24		26.5	.017
3108 10 17	10	R3/8	17	16	24		26.5	.022
3108 10 21	10	R1/2	21	16	24		26.5	.034
3108 12 13	12	R1/4	15	19	27		31	.021
3108 12 17	12	R3/8	17	19	27		31	.027
3108 12 21	12	R1/2	21	19	27		31	.041
3108 14 17	14	R3/8	20	22	30.5		35	.038
3108 14 21	14	R1/2	24	22	28.5		35	.049
3108 16 17	16	R3/8	27	27	53		38.5	.128
3108 16 21	16	R1/2	27	27	53		38.5	.124