



3606 - EQUAL TUBE TO TUBE CONNECTOR MM



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD (MM)	ØG (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾
3606 04 00	4	10	30.5	.01
3606 06 00	6	12	36.5	.016
3606 08 00	8	15	37.5	.021
3606 10 00	10	17.5	47.5	.034
3606 12 00	12	19.5	50	.042
3606 14 00	14	21.5	52.5	.05