



3809 - MALE STUD ELBOW, BSP TAPER



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	STAINLESS STEEL 316L
sub-base	STAINLESS STEEL 316L
'O'-rings	FKM
collar	STAINLESS STEEL 316L
sealing washer	STAINLESS STEEL 316L

Part Nb	ØD (MM)	C	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>
3809 04 10	4	R1/8	10	10	23.5	16.5	.02
3809 06 10	6	R1/8	13	12	27.5	20	.03
3809 06 13	6	R1/4	14	12	27.5	25	.036
3809 08 10	8	R1/8	14	15	32	25	.04
3809 08 13	8	R1/4	14	14.5	34	25	.045
3809 10 13	10	R1/4	19	17.5	37.5	27.5	.068
3809 10 17	10	R3/8	19	17.5	37.5	27.5	.069