


4890 - UNIDIRECTIONAL, FEMALE-FEMALE, BSP PARALLEL



maximum working pressure 40 bar
 4 MPa
 580 psi
working temperature -20 to 180 °C
 -4 to 356 °F
 253 to 453 °K
body STAINLESS STEEL
 316L
'O'-rings FKM
spring STAINLESS STEEL
 302

Part Nb	C	F (mm)	ØG (mm)	L (mm)	 (kg)
	All ▾	All ▾	All ▾	All ▾	All ▾
4890 10 10	G1/8	17	22	50	.082
4890 13 13	G1/4	17	22	50	.074
4890 17 17	G3/8	22	30	67	.185
4890 21 21	G1/2	24	30	71	.185
4890 27 27	G3/4	32	42	84	.288
4890 34 34	G1	38	42	90	.418