

4892 - UNIDIRECTIONAL FEMALE-MALE BSP PARALLEL



maximum working pressure 40 bar
 4 MPa
 580 psi
working temperature -20 to 180 °C
 -4 to 356 °F
 253 to 453 °K
body STAINLESS STEEL
 316L
'O'-rings FKM
spring STAINLESS STEEL
 302

Part Nb	C	F (mm)	ØG (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾
4892 10 10	G1/8	17	22	56	.09
4892 13 13	G1/4	17	22	58	.082
4892 17 17	G3/8	22	30	75	.191
4892 21 21	G1/2	24	30	79	.211
4892 27 27	G3/4	32	42	84	.314
4892 34 34	G1	38	42	102	.514