

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 04/27/05'		

NOTES:


- MATERIAL
 - INSULATOR:THERMOPLASTIC(UL 94V-0).
 - CONTACT: COPPER ALLOY.
- SPECIFICATION
 - STORAGE TEMPERATURE:-20-70°C.
 - OPERATING TEMPERATURE:0-85°C.
 - CONTACT RESISTANCE:20mΩ max.(initial).
 - INSULATION RESISTANCE:1000MΩ min.
 - DIELECTRIC WITHSTANDING VOLTAGE:AC 500V PER MINUTE.

3. PART NUMBER: DS1014

4. PRODUCT NUMBER CODE:

DS1014- X X X X

- HOUSING COLOR
 - B: BLACK
 - W: WHITE
 - L: BLUE
 - A: GRAY
- CONTACT PLATING
 - F1: FULL GOLD FLASH
- MOUNTING TYPE
 - S: V/T TYPE
 - R: R/A TYPE
 - M: SMT TYPE
 - E: Elevator TYPE
- No.OF CONTACTS
 - 10 12 14 16 20 26
 - 30 34 40 50 60 64
- SERIES No.
DS1014



Tel: 86-574-63508787

Fax: 86-574-63510817

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	BOX HEADER PITCH 2.00mm
X.	±0.60	X.	±5°	UNITS	mm	SHEET	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1014 SERIES
.XX	±0.25	.XX	±2°				
DRAWING TYPE	CUSTOMER						
SCALE	1:1	SHEET	1 OF 1				
DRAWING NO.	C-DS1014-XXXX						



晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD