


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LL 09/25/06'		



NOTES:



1. MATERIAL
  - 1.1 INSULATOR: THERMOPLASTIC (UL 94V-0).
  - 1.2 CONTACT: COPPER ALLOY.
2. SPECIFICATION
  - 2.1 STORAGE TEMPERATURE: -20-70°C.
  - 2.2 OPERATING TEMPERATURE: 0-85°C.
  - 2.3 CONTACT RESISTANCE: 20mΩ max. (initial).
  - 2.4 INSULATION RESISTANCE: 1000MΩ min.
  - 2.5 DIELECTRIC WITHSTANDING VOLTAGE: AC 500V PER MINUTE.
3. PART NUMBER: DS1012
4. PRODUCT NUMBER CODE:
 

DS1012- X X X X X X X

  - LOCK DIM.A
    - 8: 8.00mm (standard)
    - 4: 4.60mm (special)
  - HOUSING COLOR
    - A: GRAY
  - CONTACT PLATING
    - 0: SELECTIVE GOLD FLASH
  - STRAIN RELIEF
    - N: W/O
  - SCREW HOLE
    - M: W/
    - N: W/O
  - EJECTOR TYPE
    - L: Long
  - No. OF CONTACTS
    - 10 14 16 24 26
    - 30 40 50 60 64
  - SERIES No.
    - DS1012


SEE FIGURE A

$$A+21.32\pm 0.5$$




W/O SCREW HOLE


W/ SCREW HOLE



STANDARD LATCH





SPECIAL LATCH



COVER

FIGURE A



Tel: 86-574-63508787

Fax: 86-574-63510817

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE IDC SHROUDED HEADER MATES WITH PITCH 1.27mm FLAT CABLE	
X.	±0.60	X.	±5°	UNITS		mm
.X	±0.38	.X	±3'	SHEET SIZE		A4
.XX	±0.25	.XX	±2'	SERIES		DS1012 SERIES
DRAWING TYPE		CUSTOMER		<b>晨翔电子有限公司</b> <b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b>		
SCALE	1:1	SHEET	1 OF 1			
DRAWING NO.	C-DS1012-XXXXXXX					