



www.lemo.com

## **SUMMARY**

#### # Wires

Low voltage 2



Image is for illustrative purpose only

Series 0B

**Termination type** Female solder

IP rating 50

AWG wire size 28.00 - 20.00 Cable Ø 0.00 - 0.00 mm

Status active

Matching parts FGG.0B.302.CLAD42

#### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### **Mechanics**

**Shell Style/Model** EG\*: Fixed receptacle, nut fixing

Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Weight 4.26 g

#### **Performance**

Configuration 0B.302 : 2 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 10 Amps

### **Specifications**

Contact Type: Solder

Contact Dia.: 0.9 mm (0.035in) Bucket Dia.: 1.0 mm (0.039in)

Max. Solid Conductor: 0.56 mm<sup>2</sup> (AWG 20) Max. Stranded Conductor: 0.56 mm<sup>2</sup> (AWG 20)

R (max): 4.8 mOhm

Vtest (contact-shell): 1050 V (AC), 1490 V (DC) Vtest (contact-contact): 1000 V (AC), 1400 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

#### **Others**


Endurance (Shell): 5000

Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr 12NC part number: 4022.438.33190

# **DRAWINGS**



#### **Dimensions**

	A	В	E	L	М	N	<b>S</b> 1	<b>S</b> 3	e
mm.	10	12.5	7	20.7	1.2	19.1	8.2	11	M9x0.6
in.	0,39	0,49	0,28	0,81	0,05	0,75	0,32	0,43	

# **RECOMMENDED BY LEMO**

#### **Tools**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### **Cables**

CMN.02.T28.030PGCE	PVC	GREY	-
CMN.02.T28.030PGZE		Grey	-
CMN.02.T28.030PNCE	PVC	Black	-
CMN.02.T28.030PNZE			-
102080	PVC	Grey	
120184	PVC	Black	>4
120240	PVC	Black	
120250	PVC	Grey	
20140	PVC	Grey	
20140	PVC	Grey	
20141	PVC	Grey	
20142	PVC	Red	
20143	PVC	Green	
20144	PVC	Black	
20145	PVC	Yellow	=======================================
20146	PVC	Black	
20240	PTFE	White	>
20260	PVC	Black	
20264	PVC	Black	
20266	PVC	Violet	
2050	PVC	Black	-
20550	PUR	Black	-
20560	PUR	White	-
2080	PVC	Grey	
2221	PVC	Black	
2260	PTFE	White	-
2280	PVC	Black	
4082	PVC	Grey	
CCX.50.RG1.74U30B	TFE	White	
CMB.02.210.635	PUR	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.