



### Model No / Bearing

- CU3A-610ELA** / Ever Lubricate bearing (Long Life bearing)
- CU3A-610CA** / One Ball
- CU3A-610BA** / Two Ball
- CU3A-610SA** / Sleeve

### Features

- For 1U rackmount server.
- For Socket 370 up to 1.4 GHz, socket A up to 1.1 GHz.

### Specification

Overall Dimension :	60 x 60 x 23 mm
DC Fan Size :	60 x 60 x 10 mm
Base Material :	Copper
Bearing Type :	SA/CA/BA/ELA
Speed :	4800±10% RPM
Noise Level :	<32 dBA
Max Air flow :	20.26 CFM
Rated Voltage :	12 V
Weight :	200 g