



Model 3296 Adapter, Miniature Binding Posts to BNC Male







Features

Converts BNC female connection to Miniature Binding Posts and Miniature Banana Jacks

Materials

Body: Brass, Tarnish Resistant Plating Center Contact: Gold Plated Brass

Marking: "3296"

Ratings

Operating Temperautre: +50° C. (+122° F.) Max.

Operating Voltage: 500 Vrms, Maximum voltage for hands free use in controlled voltage environment.

For CE compliance, do not hold in hand when voltages exceed 30V AC / 60V DC.

Ordering Information

Model 3296

USA: Sales: 800-490-2361

Technical Support: technicalsupport@pomonatest.com

Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 International: 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.