


Weight: g/pcs

RoHS Compliant



3	Red
2	Black
1	Yellow
P1	COLOR
PIN ASSIGNMENT	

⑤	UL 1007 24T S Y L 201	UL 1007 24AWG T S 1 1 X 0.16X1.4 Y L W I R E * 1 L = 105MM	MM	105	
④	UL 1007 24T S R D 201	UL 1007 24AWG T S 1 1 X 0.16X1.4 R D W I R E * 1 L = 105MM	MM	105	
③	UL 1007 24T S B K 201	UL 1007 24AWG T S 1 1 X 0.16X1.4 B K W I R E * 1 L = 105MM	MM	105	
②	SCT 200 1 T F S 1 05	PH2.0 PHOSPHOR BRONZE TIN-PLATED TERMINAL	PCS	3	
①	SCT 200 1 H - 03 B W T 105	PH2.0 PA66 V0 WHITE 3P HOUSING	PCS	1	
No	PART NO	DESCRIPTION	UNIT	QTY	REMARK

SCONDAR
SCONDAR ELECTRONIC LIMITED

TOLERANCES: ±0.3mm

SCT P/N: HK0083-0010

UNIT: mm

PAGE/ 1 of 1

Rev A

REVISIONS			
REV	DESCRIPTION	DATE	ECN NO.
A	INITIAL RELEASE		
B			
C			
DATE		2022.09.30	
DRAWN BY		Yang	
CHECKED BY		Lisa	
APPROVED BY			
TITLE:		PH2.0 3PIN HOUSING TO TIN L=100MM	