


Weight: g/pcs

RoHS Compliant



4	Black
3	Red
2	Blue
1	White
P1	COLOR

PIN ASSIGNMENT

⑥	UL 100724T SBK201	UL 1007 24AWG TS11X0.16X1.4 BK WIRE*1 L=109MM	MM	105	
⑤	UL 100724T SBL201	UL 1007 24AWG TS11X0.16X1.4 BL WIRE*1 L=109MM	MM	105	
④	UL 100724T SRD201	UL 1007 24AWG TS11X0.16X1.4 RD WIRE*1 L=109MM	MM	105	
③	UL 100724T SWT201	UL 1007 24AWG TS11X0.16X1.4 WT WIRE*1 L=109MM	MM	105	
②	SCT2505MTPS109	SM2.5 PHOSPHOR BRONZE TIN-PLATED MALE TERMINAL	PCS	4	
①	SCT2505FH-04CBK102	SM2.5 PA66 V2 04P WITH LOCK FEMALE HOUSING COLOR:BLACK	PCS	1	

REVISIONS

REV	DESCRIPTION	DATE	ECN NO.
A	INITIAL RELEASE		
B			
C			

REVISIONS

DATE	DRAWN BY	CHECKED BY	APPROVED BY
2022.09.30	Yang	Lisa	



SCONDAR ELECTRONIC LIMITED

TOLERANCES: ±0.3mm



UNIT: mm

PAGE/ 1 of 1

SCT P/N

HK0083-0007

Rev A

CUSTOMER P/N

CUSTOMER

HK0083

TITLE:

SM2.5 4Pin Housing TO TIN L=100MM

A B C D E F G H