

PrimaVision Compact for CDM

HID-PV C 35 /I CDM 220-240V 50/60Hz

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

Product data

• General Characteristics

Rated Lamptype	CDM
Rated Number of Lamps	1 piece
Rated Ballast-Lamp Power	35
Line Voltage	220-240 V
Line Frequency	50/60 Hz
Housing	/I
Suitable for Outdoor use?	No
Lifetime 90% surv.@Tcaselife	40000 hr

• Operating Characteristics

Automatic restart	Yes
Ignition switch-off time	18 min
Ignition Voltage	4.0 (max) kV
Operating frequency *	0.14 kHz
Mains voltage safety (AC)	-18%/+10%
Mains voltage performance (AC)	-10%/+6%
Inrush current Peak	26 (max) A
Inrush current Width	0.25 ms
Earth leakage current	0.25 (max) mA
Power losses gear	4.5 W
Constant wattage deviation	-3%/+3%
PowerFactor 100% output power	0.95 -
Overvoltage protection 320Vac	48 hr

Max ballast on MCB(16A type B)	24 x
Hum and Noise level	37 dB(A)

• Wiring Characteristics

Cable-Cap output-wires mutual	150 pF
Connector type	Insert
Max. cable length Device/Lamp	2.0 m
Wcs Ballast contacts	0.50-2.50 mm ²

• Temperature Characteristics

Active temperature protection	Yes
T-case life	75 C
T-case maximum	75 (max) C
T-ambient	-20 (min), 50 (max) C
T-storage	-25 (min), 75 (max) C

• Product Dimensions

Length A1	188.0 mm
Fixing Hole Distance	170.0 mm
Length A2	
Width B1	82.7 mm
Height C1	34.5 mm
Fixing Hole Diameter D1	4.8 mm

• Approval & Application Chars

EMI 9 kHz ... 300MHz	CISPR 15 ed 7.2
Safety Standard	EN 61347-2-12
Quality Standard	ISO 9000:2000

PHILIPS

PrimaVision Compact for CDM



Environmental Standard	ISO 14001
Harmonic current emissions	EN 61000-3-2
EMC Immunity	EN 61547
Vibrations	IEC 68-2-6 Fc
Bumps	IEC 68-2-29 Eb
Humidity	IEC 928-13
Approval marks	ENEC
CE marking	Yes
Temperature marking	F

Full product code	872790085973700
Full product name	HID-PV C 35 /I CDM 220-240V 50/60Hz
Order product name	HID-PV C 35 /I CDM 220-240V 50/60Hz
Pieces per pack	1
Packing configuration	12
Packs per outerbox	12
Bar code on pack - EAN1	8711500881700
Bar code on outerbox - EAN3	8727900859737
Logistic code(s) - 12NC	913700653166
Net weight per piece	0.360 kg

• Product Data


Order code	859737 00
------------	-----------

Dimensional drawing



HID-PV C 35 /I CDM 220-240V 50/60Hz

Product	A1 (Norm)	A2 (Norm)	B1 (Norm)	B2 (Norm)	C1 (Norm)	D1 (Norm)
HID-PV C 35 /I CDM 220-240V 50/60Hz NG	188.0	170.0	82.7	-	34.5	4.8



HID-PV CDM Gen 4.3



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, February 10
data subject to change