




## NOTES:

- 1. INSTALLATION:
  - 1. INSTALL THE JACK AND THE WASHER (IF NEEDED) FROM THE BACK OF THE PANEL.
  - 2. INSTALL THE ORING AND THEN THE HEX NUT FROM THE FRON OF THE PANEL.
  - 3. TIGHTEN THE NUT.
  - 4. SEE THE TABLE BELOW FOR INSTALLATION INSTRUCTIONS:

Panel thickness /Inches	0.050	0.055	0.060	0.065	0.070	0.075	0.080	0.085	0.090	0.095	0.100	0.105	0.110	0.115	0.120	0.125	
Kit part number		W07 (LARGE)								W11 (SMALL)							
Washer (K180)	yes yes yes yes yes no no no no yes yes yes yes yes no										no						

- 2. HEX NUT FINISH: NICKEL
- 3. TO BE USED WITH 267S15-S28 PLUGS.
- 4. IP RATING: IP66
- 5. RECOMMENDED HOLE DIAMETER: Ø0.375" [9.5MM]
- 6. RECOMMENDED WORKING TEMPERATURE: -20TO 50 °C.
- 7. RoHS COMPLIANT.



## **CUSTOMER DRAWING**

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPE BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDE										
					UNLESS OTHERWISE SPECIFIED	SIZE *	٧	WIDTH * MUL		*	LBS/M *		TEMP	ER *	
					1. ALL DIMENSIONS IN INCHES [mm]	FINISH	*			MATERI	MATERIAL			*	
					- TWO PLACE DECIMALS ±0.02 [0.5]	SPEC No.	<b>*</b>			SPEC No. *					
					- THREE PLACE DECIMALS ±0.005 [0.13]	-   -		N SCALE 1:1						⇒ GCL®	
								CHK	'" '-		Swife				
	555111111151	011=100		000				NS	SRC						
0A	PRELIMINARY	2/17/20	NS	SRC		2/1//20	110	2/17/2	0 2/17/20		SHEET	1	OF	1	
REV	ECO NUMBER	DATE	BY	APVD		NAME			•	PART No				REV	
REVISIONS					DO NOT SCALE DRAWING	SEALED 1/4" JACK				12BW07-W11			0A		