

Прибор	Уиз	Риз/У	Упр/Inp	Inp/лим	Уком	Io/Iom	Укэ/к	Т	Кор-
	В	ГОм/В	В/мА	мА/мА	В	мА/мА	В /мА	мкс	пус
АОТ101АС	1500	100/500	1.6/5	20/50	15	5/	0.4/0.5	10	54
АОТ101БС	1500	100/500	1.6/5	20/50	10	10/	0.4/10	10	54
АОТ101ВС	1500	100/500	1.6/5	20/50	10	5/	0.4/0.5		54
АОТ101ГС	1500	100/500	1.6/5	20/50	15	5/	0.4/0.5		54
АОТ101ДС	1500	100/500	1.6/5	20/50	15	10/	0.4/10		54
АОТ101ЕС	1500	100/500	1.6/5	20/50	15	10/	0.4/10		54
АОТ101ЖС	1500	100/500	1.6/5	20/50	30	10/	0.4/2.5		54
АОТ101ИС	1500	100/500	1.6/5	20/50	15	10/	0.4/2.5		54
АОТ102А	500	0.1/500	2.0/15	40/150	30	50/1 А	4/50	5	40
АОТ102Б	500	0.1/500	2.0/15	40/150	30	50/1 А	4/50	5	40
АОТ102В	500	0.1/500	2.0/15	40/150	30	50/1 А	4/50	5	40
АОТ102Г	500	0.1/500	2.0/15	40/150	30	50/1 А	4/50	5	40
АОТ110А	500	1/500	2.0/25	30/100	30	200/200	1.5/200	100	41
АОТ110Б	500	1/500	2.0/25	30/100	50	100/100	1.5/100	100	41
АОТ110В	500	1/500	2.0/25	30/100	30	100/100	1.5/100	100	41
АОТ110Г	500	1/500	2.0/25	30/100	15	200/200	1.5/200	100	41
АОТ110Д	500	1/500	2.0/25	30/100	50	200/200	1.5/200		41
ЗОТ122А	100	1/100	1.6/5	15/85	50	15/15	1.5/15	100	42
ЗОТ122Б	100	1/100	1.6/5	15/85	30	25/25	1.5/25	100	42
ЗОТ122В	100	1/100	1.6/5	15/85	30	15/15	1.5/15	100	42
ЗОТ122Г	100	1/100	1.6/5	15/85	15	15/15	1.5/15	100	42
АОТ123А	100	1/100	2.0/20	30/100	50	10/	0.3/10	2	43
АОТ123Б	100	1/100	2.0/20	30/100	30	20/	0.5/20	4	43
АОТ123В	100	1/100	2.0/20	30/100	30	10/	0.3/10	2	43
АОТ123Г	100	1/100	2.0/20	30/100	15	20/	0.5/20	4	43
АОТ126А	1000	100/500	2.0/20	30/100	30	10/10	0.3/10	2	43
АОТ126Б	1000	100/500	2.0/20	30/100	15	10/10	0.3/10	2	43
ЗОТ127А	500	100/500	1.6/5	15/100	30	70/70	1.5/70	100	41
ЗОТ127Б	500	100/500	1.6/5	15/100	30	70/70	1.5/15	100	41
ЗОТ127В	500	100/500	1.6/5	15/	15	70/70	1.5/15	100	41
АОТ127А	500	100/500	1.6/5	15/100	30	70/70	1.5/70	100	46
АОТ127Б	500	100/500	1.6/5	15/100	30	70/70	1.5/15	100	46
АОТ127В	500	100/500	1.6/5	15/	15	70/70	1.5/15	100	46
АОТ128А	1500	100/500	1.6/10	40/100	50	8/8	0.3/2.5	5	49
АОТ128Б	1500	100/500	1.6/10	40/100	30	32/32	0.4/10	5	49
АОТ128В	1500	100/500	1.6/10	40/100	30	16/16	0.4/5	5	49
АОТ128Г	1500	100/500	1.6/10	40/100	15	16/16	0.4/5	5	49
АОТ128Д	1500	100/500	1.6/10	40/100	50	32/100	0.3/10	10	49
ЗОТ131А	1000	100/500	1.7/30	30/50	15	10/10	1.5/10		41
ЗОТ135А	1000	100/500	1.6/20	20/85	30	200/200	1.5/100		41
ЗОТ135Б	1000	100/500	1.6/20	20/85	15	200/200	1.5/100		41
ЗОТ136А	1000	100/500	1.6/10	10/50	15	20/20	1.2/20		41
ЗОТ136Б	1000	100/500	1.6/10	10/50	30	20/20	1.2/3		41
АОТ137А			1.8/10	30/50	5		0.4/0.02		48
АОТ137Б			1.8/10	30/50	5		0.4/0.1		48
АОТ137В			1.8/10	30/50	5		0.4/0.02		48
АОТ137А1			1.8/10	30/50	5		0.4/0.02		58
АОТ137Б1			1.8/10	30/50	5		0.4/0.1		58
АОТ137В1			1.8/10	30/50	5		0.4/0.02		58
ЗОТ138А	1000	100/500	1.8/25	25/50	30	10/10	0.3/4		43
ЗОТ138Б	1000	100/500	1.8/25	25/50	30	20/20	0.4/8		43
ЗОТ142А	10000	100/500	1.8/30	30/100	30	50/50	1.5/25		44
ЗОТ142Б	10000	100/500	1.8/30	30/100	15	50/50	1.5/50		44
ЗОТ144А	3000	100/500	1.8/25	25/50	30	25/25	0.3/10		53
ЗОТ146А			1.8/10	30/100	30		0.4/20		56
ЗОТ146Б			1.8/30	30/100	15		0.4/50		56
АОТ147А	8000	100/500	1.8/10	30/100	30	1.5/	0.4/1		50
АОТ147Б	8000	100/500	1.8/10	30/100	15	3.0/	0.4/2		50
АОТ147В			1.8/	30/100	15	0.36/	0.4/0.12		50
АОТ147Г			1.8/	30/100	15	0.12	0.4/0.04		50
ЗОТ150А	3000	100/500	1.8/20	20/50	15	100/100	1.5/100		53
ЗОТ150Б	3000	100/500	1.8/20	20/50	30	100/100	1.5/100		53
АОТ151А	8000		1.8/10	30/100	30		0.4/0.1		59