



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes: AWG#22~28#

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01		料号 PART NO.	HC-PHD-T		版本 REV.	A
			X. \pm 0.25	X. \pm 2'		审核 CHECK	张名 2013、07、03		品名 TITLE	PHDC带钩端子		
			.X \pm 0.20	.X \pm 1'	核准 APPROVAL	张名 2013、07、05		客户料号 CUTL. NO.				
			.XX \pm 0.15	.XX \pm 0.5'	单位 UNITS	MM	比例 SCALE	1:1	深圳市华灿天禄电子有限公司			
			.XXX \pm 0.10	.XXX \pm 0.5'								