



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE $\pm 0.05$ )

SPECIFICATIONS  
 Rated Current:3.0AMP  
 Contact Resistance:20m $\Omega$  Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000M $\Omega$  Min  
 Operation Temperature:-40 $^{\circ}$ c to +105 $^{\circ}$ c

Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230 $^{\circ}$ C for 30-60 seconds  
 (260 $^{\circ}$ C for 10 seconds)

Dimension antitheses list			
ITEM	PA	PB	PC
Standard	6.00	6.90	3.00
Alternate			

**Ordering Information**

PZ 254 - \* - N - W - 8.5 - \*\*

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2=40Pin 4=80Pin 8=160Pin	Type N=直插 W=弯插 S=贴片	Contact Plating G0:Gold Flush G1:1 $\mu$ " Gold G2:3 $\mu$ " Gold G3:5 $\mu$ " Gold G4:10 $\mu$ " Gold G5:15 $\mu$ " Gold G6:30 $\mu$ " Gold S0:Gold Flash/Tin S1:Tin
---	---	------------------------------	--

			GENERAL TOLERANCE	制图	<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	DRAWING				
			X.X $\pm 0.30$	审核	产品名称	2.54双排 排针 正弯(塑高2.5)	版本	A
			X.XX $\pm 0.20$	检查	TITLE		REV.	
			X.XXX $\pm 0.10$	批准	PART NO.	PZ254-2-N-W-8.5-XX	单位	mm
序号	变更内容	日期	Angle $\pm 3.0^{\circ}$	投影	材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE		Projection	MATERIAL		SHEET	