



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25° C~85° C.
 3. 额定电压: 50V, AC, DC.
 4. 接触电阻: ≤0.02Ω.
 5. 绝缘电阻: ≤100MΩ



Pin	A	B	C	D
2	1.25	4.40	3.20	
3	2.50	5.65	4.45	
4	3.75	6.90	5.70	2.50
5	5.00	8.15	6.95	3.75
6	6.25	9.40	8.20	5.00
7	7.50	10.65	9.45	6.25
8	8.75	11.90	10.70	7.50
9	10.00	13.15	11.95	8.75
10	11.25	14.40	13.20	10.00
11	12.50	15.65	14.45	11.25
12	13.75	16.90	15.70	12.50
13	15.00	18.15	16.95	13.75
14	16.25	19.40	18.20	15.00
15	17.50	20.65	19.45	16.25
16	18.75	21.90	20.70	17.50

APPROVALS

DRAWN	G.M.Chen	DATE	2015/7/17
CHECKED			
APPROVALS			

TOLERANCES ARE

30 ^{±0.15}	±0.30	ANGLE
10 ^{±0.10}	±0.20	
5 ^{±0.10}	±0.15	±2°
~ 5	±0.10	

TITLE: 1.0 Pitch 直插

PART NO. 1.25-XXAW

SCALE: 1:1

SHEET 1 OF 1

PROJ. 1

DEALON 德之隆 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			