

1. Material:

1.1. Housing: Material: PA Nylon UL94V-0
Color: Black

2. Electrical performance:

2.1. Insulation resistance: 100MΩ MIN



3. The product environmental requirements.

3.1. Work temperature: -25°C ~ +85°C

4. Product environmental protection level:

4.1. Products comply with RoHS standards

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-1.2-2Y	1.20	2.60
3	HC-1.2-3Y	2.40	3.80
4	HC-1.2-4Y	3.60	5.00
5	HC-1.2-5Y	4.80	6.20
6	HC-1.2-6Y	6.00	7.40
7	HC-1.2-7Y	7.20	8.60

			GENERAL TOLERANCE		制图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK		产品名称 TITLE		版本 REV.	A
			X. X	±0.20	批准 APPROVAL		Customer drawing for 1.2 (无卤) XP Housing			
			X. XX	±0.15	比例 SCALE		产品料号 PART NO.		单位 UNITS	mm
			X. XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle	±2.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								