



**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer Nylon46,UL94V-0  
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-XA-2AW	2.50	7.50
3	HC-XA-3AW	5.00	10.00
4	HC-XA-4AW	7.50	12.50
5	HC-XA-5AW	10.00	15.00
6	HC-XA-6AW	12.50	17.50
7	HC-XA-7AW	15.00	20.00
8	HC-XA-8AW	17.50	22.50
9	HC-XA-9AW	20.00	25.00
10	HC-XA-10AW	22.50	27.50
11	HC-XA-11AW	25.00	30.00
12	HC-XA-12AW	27.50	32.50

**PCB LAYOUT**

**2~5A**

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	2.5 弯针	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-XA-NAW	单位 UNITS	mm
1	初版发行		X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投影 Projection				
			Angle ±3.0°					