

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LL 01/13/07		


NOTES:

- SPECIFICATIONS
  - Contact Resistance: 50mΩ max
  - Insulator Resistance: 100MΩ min.
  - Current Rating: 1.5 A.
  - Rated Voltage: 30V DC
  - Dielectric withstanding voltage: AC 100V For 1 minute
  - Contact: Copper Alloy
  - Housing: Thermoplastic(UL 94V-0)

2. PRODUCT NUMBER CODE:

DS1102 - X X X

- Contact plating  
C: Selective 3u" gold
- Shell plating  
N: Nickel  
6: Tin
- Color of housing  
B: Black



RECOMMEND P.C.B LAYOUT(TOLERANCE±0.05)

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5°	mm	IEEE 1394 Female 6PIN SMD TYPE
.X	±0.38	.X	±3°		
.XX	±0.25	.XX	±2°		
DRAWING TYPE	CUSTOMER	SHEET SIZE	A4	SERIES	DS1102
SCALE	1:1	SHEET	1 OF 1		
DRAWING NO.	C-DS1102-XXX				

晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD

Tel: 86-574-63508787  
Fax: 86-574-63510817