

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	HP 23/06/05		

NOTES:




1. SPECIFICATIONS

- . Contact Resistance: 30mΩ max
- . Insulator Resistance: 1000MΩ min.
- . Current Rating: 30V DC 1.5 A max
- . Dielectric withstanding voltage: AC500V For 1 minute
- . Contact: Copper alloy
- . Housing: PBT.

2. PRODUCT NUMBER CODE:

DS1108 - X X X


- Color of housing  
W: white  
B: black
- Shell plating  
6: tin  
N: nickel  
8: full gold
- Contact plating  
0: selective gold flash  
C 3u" gold  
3: 30u" gold



Tel: 86-574-63508787

Fax: 86-574-63510817

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE	
X. ±0.60	.X ±0.38	.X ±5°	.X ±3°	mm	USB-B MALE SOLDER	
.XX ±0.25		.XX ±2°			SHEET SIZE	A4
DRAWING TYPE		CUSTOMER			SERIES	DS1108
SCALE		1:1	SHEET	1 OF 1		
DRAWING NO.		C-DS1108-XXX				

 晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD