



175 series

MINI USB-A FEMALE 5PIN
SMT & DIP

Specifications:

Contact Resistance: 10m Ω max.
Insulator Resistance: 500M Ω min.at DC 500V
Current Rating: 24V DC 1AMP max

Dielectric Withstanding:

Voltage: AC 500V For 1 minute
Contact: Brass
Housing: PBT & 30% Glass Fiber(UL 94V-0)

