



178 series

USB-A FEMALE SOLDER


Specifications:

Contact Resistance: 10m Ω max.
 Insulator Resistance: 500M Ω min.at DC 500V
 Current Rating: 24V DC 1AMP max

Dielectric Withstanding:

Voltage: AC 500V For 1 minute
 Contact: Brass
 Housing: PBT &30% Glass Fiber(UL 94V-0)

[A TYPE]



[B TYPE]

