


XY2500F-A(5.0)

XY2500F-B(5.08)

Poles: Any poles(2-24P)

Pitch: 5.0mm 5.08mm



Voltage Rating: 300V

Current Rating: 12A

Wire range: 18-12AWG 2.5mm²

Housing: PA66 (UL 94V-0)

Wire Cage: Brass(Nickel Plated)or
Steel(Zinc Plated)

Clamp: Phosphor Bronze, Tin Plated

Screw: M2.5, Steel(Q235), Zinc Plated

Torque: 0.4N.m

额定电压: 300V

额定电流: 12A

使用线径: 18-12AWG 2.5mm²

塑件: 尼龙66 (UL 94V-0)

接触保护材料: 黄铜, 镀镍

或铁, 镀锌

弹片(触点)材料: 磷青铜, 镀锡

螺丝材料: M2.5, Q235钢, 镀锌

扭矩: 0.4N.m

