

XY126V

Poles: 2P & 3P
Pitch: 5mm



Voltage Rating: 250V
Current Rating: 10A
Wire range: 26-14AWG 1.5mm²
Housing: PA66(UL 94V-0)
Wire Protector: Stainless Steel
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel(Q235), Zinc Plated
Torque: 0.4N.m

额定电压: 250V
额定电流: 10A
使用线径: 26-14AWG 1.5mm²
塑件: 尼龙66 (UL 94V-0)
压线簧片: 不锈钢
触点材料: 黄铜, 镀锡
螺丝材料: M2.5, Q235钢, 镀锌
扭矩: 0.4N.m

