


XY128V-A

Poles: 2P/3P/4P/5P
Pitch: 5.0mm



Voltage Rating: 250V
Current Rating: 10A
Wire range: 18-12AWG 2.5mm²
Housing: PA66 (UL 94V-0)
Wire Cage: Steel, Zinc Plated
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel (Q235), Zinc Plated
Torque: 0.4N.m

额定电压: 250V
额定电流: 10A
使用线径: 18-12AWG 2.5mm²
塑件: 尼龙66 (UL 94V-0)
接触保护材料: 铁, 镀锌
触点材料: 黄铜, 镀锡
螺丝材料: M2.5, Q235钢, 镀锌
扭矩: 0.4N.m

