


XY122R

Poles: Any poles
Pitch: 5.08mm



Voltage Rating: 250V
Current Rating: 10A
Wire range: 22-14AWG 1.5mm²
Housing: PA66(UL 94V-0)
Clamping: SUS301
Solder Pin: Brass, Tin Plated

额定电压: 250V
额定电流: 10A
使用线径: 22-14AWG 1.5mm²
塑件: 尼龙66 (UL 94V-0)
弹片: 不锈钢SUS301
触点材料: 黄铜, 镀锡

