

XY130

Poles: 2P & 3P
Pitch: 9.5mm



Voltage Rating: 250V
Current Rating: 16A
Wire range: 26-10AWG 6.0mm²
Housing: PA66 (UL 94V-0)
Wire Cage: Steel, Zinc Plated
Solder Pin: Brass, Tin Plated
Screw: M3.0, Steel (Q235), Zinc Plated
Torque: 0.5N.m

额定电压: 250V
额定电流: 16A
使用线径: 26-10AWG 6.0mm²
塑件: 尼龙66 (UL 94V-0)
接触保护材料: 铁, 镀锌
触点材料: 黄铜, 镀锡
螺丝材料: M3.0, Q235钢, 镀锌
扭矩: 0.5N.m

