

# XY825A

Poles: Any poles(2-33P)  
Pitch: 7.62mm



Voltage Rating: 300V  
Current Rating: 10A  
Wire range: 22-14AWG 1.5mm<sup>2</sup>  
Housing: PA66 (UL 94V-0)  
Solder Pin: Brass, Tin Plated  
Screw: M3, Steel(Q235), Zinc Plated  
Torque: 0.8N.m

额定电压: 300V  
额定电流: 10A  
使用线径: 22-14AWG 1.5mm<sup>2</sup>  
塑件: 尼龙66 (UL 94V-0)  
端子材料: 黄铜, 镀锡  
螺丝材料: M3, Q235钢, 镀锌  
扭矩: 0.8N.m

