

## Specification Sheet

Part Number: 556-00256

300 dpi print head for high resolution printing.

Label holder included for easy loading of any size media.

Lightweight with a small footprint for easy transport to jobs sites or around the shop.

LCD user interface for easier setup, diagnostics and adjustments.

Ethernet ready for easy network connectivity.

Print speeds up to 3 in (76.2mm) per second for fast label production.

2mb flash/8mb DRAM for accepting large label files that require a lot of data.

Highly accurate sensor means there is no need to calibrate during label changes and eliminates most common printer errors.



TT230SMC Printer Kit with Cutter, 1/pkg

<b>Article Number</b>	556-00256
<b>Type</b>	TT230SMC KIT
<b>Color</b>	Black (BK)
<b>Quantity Per</b>	EA

<b>Product Description</b>	HellermannTyton's TT230 Series thermal transfer printers are designed for low- to medium-volume printing of thermal transfer labels and ShrinkTrak. They deliver optimal performance not found in other small desktop printers. This lightweight printer offers high speed, precision and flexible printing with the ability to print on most HellermannTyton labels and ShrinkTrak. Used in conjunction with TagPrint Pro, the printers offer error-free printing and seamless operation. Each kit contains one TT230SMC printer (556-00240), a carrying case (556-00231), one black and one white ribbon (TT822OUTSM) and (556-00190), label holder (556-00235) and TagPrint Pro 4.0 software (556-00035).
<b>Short Description</b>	TT230SMC Printer Kit with Cutter, 1/pkg
<b>Global Part Name</b>	TT230SMC KIT-PL-BK
<b>Technical Description</b>	TT230SMC Kit
<b>Contents of pkg/kit</b>	One TT230SMC printer with cutter, label caddy, TagPrint® Pro label design software, black ribbon, white ribbon, and a high-quality hard-shell carrying case.
<b>Length L (Imperial)</b>	11.75
<b>Length L (Metric)</b>	298.5
<b>Width W (Imperial)</b>	7.95
<b>Width W (Metric)</b>	202
<b>Height H (Imperial)</b>	13.5
<b>Height H (Metric)</b>	342.9

<b>Material</b>	Plastic (PL)
<b>Material Shortcut</b>	PL
<b>Halogen Free</b>	No
<b>Operating Temperature</b>	+40°F to +104°F (+4°C to +40°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>Package Quantity (Imperial)</b>	1
<b>Package Quantity (Metric)</b>	1
<b>Customs Number</b>	8443321050