

USB-C to Gigabit Network Adapter with Thunderbolt 3 Compatibility - Black

MODEL NUMBER: U436-06N-GB



Easily connect your PC, laptop or tablet to a Gigabit Ethernet network with this ultra-compact USB to LAN converter.

Features

Instantly Connect to a Gigabit Network on Your Laptop or Desktop Computer

Enjoy Fast, Simple Connections Every Time

Access True Gigabit Speeds Without an Ethernet Card

Take It with You Wherever You Go

Highlights

- Connects a USB-C or Thunderbolt 3 PC, laptop or tablet to a wired Ethernet network
- Provides instant access to Gigabit speeds without an internal Ethernet card
- Simplified connections with a reversible Type-C connector that plugs into your device's port in any direction
- Easy to install with plug-and-play operation—no software or drivers required
- Ultra-compact design for easy transport

Applications

- Add a wired network connection to your PC or MacBook Pro when wireless connectivity is unreliable
- Plug into a convention center's wired Ethernet network at a trade show or sales conference
- Take advantage of Gigabit network speeds to download large files rapidly
- Stream audio and video over the Internet without fear of losing your signal

System Requirements

- Windows, Mac or Chromium operating system
- USB-C or Thunderbolt 3 port

Package Includes

- USB-C to Gigabit Network



Adapter with Thunderbolt 3

Compatibility – Black

- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332206954
Technology	Cat5/5e; Cat6; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
INPUT	
Built-In Cable Length (ft.)	0.3
Built-In Cable Length (m)	0.1
Built-In Cable Length (in.)	3.9
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
USB Power Delivery (PD) Charging Support	No
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	0.79 x 4.75 x 3.94
Shipping Weight (lbs.)	0.13
Unit Dimensions (hwd / in.)	0.63 x 1.1 x 2.36
Unit Packaging Type	Box
Unit Weight (kg)	0.03



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (lbs.)	0.06
ENVIRONMENTAL	
Operating Temperature Range	32 to 158 F (0 to 70 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	3.1
Power Consumption (Watts)	1
Power Consumption Detail	1W Maximum
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
CONNECTIONS	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	RJ45 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
UASP Support	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>